

# THC 5000

REINVENTING CONTINUITY . . .

**NEW**

Also available in  
AIR, CO<sub>2</sub> and O<sub>2</sub>

Continuous analysis  
of THC in N<sub>2</sub>, Ar, He, H<sub>2</sub>



Address: 7125 North Loop East  
Houston, TX 77028  
Phone: 713-947-9591  
Fax: 713-947-7549  
e-mail: [cosa@cosaic.com](mailto:cosa@cosaic.com)  
Internet: [www.cosa-instrument.com](http://www.cosa-instrument.com)

# THC 5000 Continuous analysis of THC (as methane equivalent) in N<sub>2</sub>, Ar, He, H<sub>2</sub>

## General characteristics

- Continuous measurement system based on a flame ionization detector.
- System controlled by microprocessor.
- Easy to use.
- Easy maintenance.
- Low sample flow.
- Less power consumption.
- CE Analyzer.
- Alphanumeric screen 8 x 40 characters, 64 x 240 pixels.
- Multifunctional and real-time software.

## Dimensions


- Height ..... 7"
- Width ..... 19"
- Depth ..... 19"

## Technical characteristics

- Three ranges:
  - 0-1 ppm ..... display resolution 0.01 ppm
  - 0-10 ppm ..... display resolution 0.1 ppm
  - 0-100 ppm ..... display resolution 0.1 ppm
- Accuracy: 0.5% of the reading scale
- Detection limit <0.05 ppm on the range 0-1 ppm
- Drift ..... 1 % during 24 hours  
(0.5% over a longer period)

- Gas connections
  - Sample ..... 1/8" Swagelok SS
  - Air ..... 1/8" Swagelok SS
  - H<sub>2</sub> ..... 1/8" Swagelok SS
- Sample flow ..... ± 3 l/h
- Max Input Pressure ..... working pressure from 4 to 220 psi
- Synthetic air
  - Flow ..... 20 l/h
  - Pressure ..... 29 psi
  - Purity ..... 5.0
- Hydrogen
  - Flow ..... 2 l/h
  - Pressure ..... 15 psi
  - Purity ..... 6.0
- Working Temperature ..... ambient and stable temperature (+/- 68 °C)
- Power supply ..... 110 Vac, 50-60 Hz
- Consumption ..... 500 VA
- Output 4-20 mA ..... 1 output for THC impurity
- Connector RJ-45 ..... computing maintenance of the system
- Output relays ..... (dry contacts, SPST 2A/250 Vac)
  - 1 STATUS contact relay (security alarm)
  - 3 RANGE contact relays (active range)
  - 1 process alarm contact relay (level 1)
  - 1 process alarm contact relay (level 2)
  - 2 contacts for automatic calibration

# THC 5000



\* Optional